


**FEATURES:**

1. HEPA FILTER ASSURES 99.99% FILTRATION EFFICIENCY FOR PARTICLES Ø3 MICRONS AND LARGER
2. LIGHTWEIGHT ANODIZED ALUMINUM FRAMEWORK RIGIDLY CLAMPED TOGETHER.
3. EASILY DETACHABLE TABLE AND CABINET ALLOWS FOR EASY SITE ASSEMBLY AND MOVING THRU DOORWAYS.
4. BACKWARD CURVED FANS WITH SPEED CONTROL.
5. FRONT FILTER REMOVAL, PERFORATED FILTER GRILL.
6. PREFILTER GRILL, 30% PREFILTERS REMOVED FROM THE FRONT.
7. STATIONS MAY BE INSTALLED TO END WITH ELECTRICAL AND PNEUMATICS RUNNING STATION TO STATION.

**OPTIONS:**


1. UP TO SIX DUPLEX RECEPTACLES INTERNALLY WIRED AND SEALED.
2. POWDER COATED FRAMEWORK.
3. UL RATED LIGHT FIXTURES.
4. CUSTOMER SPECIFIED TABLE HEIGHT AND DEPTH.
5. STAINLESS STEEL OR HIGH WEAR TABLE TOPS.
6. POWER CORD.
7. IONIZING BARS
8. PVC, POLYPROPYLENE OR PLASTIC CORE ALUMINUM PANELS.

| MODEL     | LENGTH | WIDTH | HEIGHT | OPTIONAL HEIGHT | CFM  | BASE UNIT WT. (LBS) |
|-----------|--------|-------|--------|-----------------|------|---------------------|
| SINGLE 48 | 48"    | 14"   | 49"    | 51"             | 300  | 160                 |
| SINGLE T2 | T2"    | 14"   | 49"    | 51"             | 450  | 200                 |
| SINGLE 96 | 96"    | 14"   | 49"    | 51"             | 600  | 240                 |
| DUAL 48   | 48"    | 14"   | 49"    | 51"             | 600  | 220                 |
| DUAL T2   | T2"    | 14"   | 49"    | 51"             | 900  | 270                 |
| DUAL 96   | 96"    | 14"   | 49"    | 51"             | 1200 | 330                 |



FILTER AREA

LENGTH



LEG LEVELERS

WIDTH

BASE HEIGHT

ACCESS PANEL

PREFILTER GRILL

OPTIONAL LAMINATED TABLE TOP, ROUNDED FRONT EDGE

34"

15 1/2"

33"

OPTIONAL SHELF

30"

4'-8 1/2"

OPTIONAL ELECTRICAL AND PNEUMATIC CONNECTIONS

OPTIONAL CABINET WITH SLIDING DOORS

OPTIONAL DUPLEX RECEPTACLES

DOUBLE SIDED UNIT WITH TABLE, SHELF AND CABINET

**SHEET CONTENT**

CROSS FLOW ASSEMBLY WORKSTATION

SCALE: 1/2"=1'-0" DATE ISSUED: 12-6-04

JOB #: FILE PATH:

DRAWN BY: GAM  
CHECKED BY: XXX

APPROVED BY: DATE:

SHEET NUMBER

**CROSSFLOW ASSEMBLY  
WORKSTATION**

